

Digital Compact Scale

# HL-i


Series

*HL-i series compact design makes it highly suitable for weighing applications at work, school, home or anywhere*



**Nin★JA**

New Innovative Novel Japanese Apparatus



**Batteries  
Included**



**A&D**

...Clearly a Better Value

A&D Company, Limited  
<http://www.aandd.jp>

## // High Weighing Resolution of 1/2000

Precision weighing of 200g x 0.1g for HL-200i and 2000g x 1g for HL-2000i

## // Calibration Function

Easy and simple to calibrate the scale with external calibration mass for accurate weighing

## // Multi Weighing Units

Meet any weighing application with weighing units of g, oz, ct and tael for HL-200i and g, oz, lb-oz and tael for HL-2000i

## // Two Way Power

Use either 4 x AA batteries or the optional AC adapter

## // Long Battery Life

Continuous operation for 1000 hours using alkaline batteries

## // Tare Function to Full Weighing Capacity

One touch tare using the "RE-ZERO" key enables the user to use a weighing container and still benefit from the full weighing range of the scale!

## // Large LCD Display

Easy to read 13.5mm LCD display

## // Large Weighing Pan

Easily weigh large objects on the 130mm diameter weighing pan

## // Auto Power Off Function

Save battery life with the Auto Power Off function. HL-i automatically shuts down after 5 minutes of disuse

## // Low Battery Indication

Low battery warning is displayed when the batteries are running low

## // Overload Indication

Display indicator for scale overload conditions

## // Stable Indicator

Lets you know when the scale is stable and ready to weigh ensuring accurate weighing results

## // Compact Size

Small size means it's easy to use anywhere. The scale can also be stored on its side or rear, saving space!

### HL-i Series Specifications

|                       | HL-200i   | HL-2000i             |
|-----------------------|---|----------------------|
| Capacity x Resolution | 200g x 0.1 g  | 2000 g x 1 g         |
|                       | 7.05 oz x 0.01 oz   | 70.5 oz x 0.1 oz     |
|                       | 1000.0 ct x 0.5 ct  | 4 lb 6.6 oz x 0.1 oz |
|                       | 5.335 tl x 0.005 tl *                                       | 53.35 tl x 0.05 tl * |
| Non-linearity         | ±0.2g   | ±2g                  |
| Repeatability         | 0.1g  | 1g                   |
| Span drift            | ±0.015% / °C TYP (5°C~35°C / 41°F~95°F)                     |                      |
| Operating temp.       | - 10°C~40°C / 14°F~104°F, Less than 85%RH                   |                      |
| Display               | 13.5 mm / 0.53 in., 7segment liquid crystal display         |                      |
| Display update        | Approximately 5 times per second                            |                      |
| Power                 | 4 x "AA" size batteries or AC adapter                       |                      |
| Battery life          | Approximately 1000 hours with alkaline cells at 20°C / 68°F |                      |
| Pan size              | 130mm / 5.1in.  |                      |
| Dimensions            | 130(W)x192(D)x51(H)mm / 5.1(W)x7.6(D)x2.0(H)in.             |                      |
| Weight                | Approximately 500g / 1.1lb                                  |                      |
| Calibration weight    | 200g  | 2000g                |
| Option                | AC adapter  |                      |

\* tl : Taiwan tael

### Options

AX-TB-196 AC100V with A plug  
 AX-TB-202 AC120V with A plug  
 AX-TB-164 AC220-230V with C plug  
 AX-TB-173 AC220-230V with BF plug  
 AX-TB-172 AC220-240V with S plug



# Nin★JA

New Innovative Novel Japanese Apparatus

# AND

...Clearly a Better Value

**A&D Company, Limited**

3-23-14 Higashi-Ikebukuro, Toshima-ku, Tokyo 170-0013 JAPAN  
 Telephone:[81](3) 5391-6132 Fax:[81](3) 5391-6148  
 http://www.aandd.jp

**A&D ENGINEERING, INC.**

1555 McCandless Drive, Milpitas, CA. 95035 U.S.A.  
 Telephone:[1](408) 263-5333 Fax:[1](408) 263-0119

**A&D MERCURY PTY. LTD.**

32 Dew Street, Thebarton, South Australia 5031 AUSTRALIA  
 Telephone:[61](8) 8301-8100 Fax:[61](8) 8352-7409

**A&D INSTRUMENTS LTD.**

Unit 24/26 Blacklands Way Abingdon Business Park,  
 Abingdon, Oxon OX14 1DY United Kingdom  
 Telephone:[44](1235) 550420 Fax:[44](1235) 550485

**<German Sales Office>**

Große Straße 13 b 22926 Ahrensburg GERMANY  
 Telephone:[49](0) 4102 459230 Fax:[49](0) 4102 459231

**A&D KOREA Limited**

Manhattan Bldg. 8F, 36-2 Yoido-dong, Youngdeungpo-gu, Seoul, KOREA  
 Telephone:[82](2) 780-4101 Fax:[82](2) 782-4280